


CONNECTING CABLE

CSTE02008

Order no.	CSTE02008
Technical Data	
Fixing thread	M12-M12
Connection type	Pin / socket
Coding	A
Version	Straight/straight
No. of contacts	5
Rated voltage [V]	60
Current load (at 40°C) [A]	4
Grip body material	PUR
Coupling nut material	Metal, CuZn, nickel-plated
Sealing material	FKM
Cable sheath material	PUR
Cable length [m]	5
Cable-Ø [mm]	7.0
Nr. of wires x diameter [mm ²]	2x0.25+2x0.34
Bending radius for fixed routing, min.	6xØ
Bending radius when using a drag chain, min.	10xØ
Temperature range (fixed) min. [°C]	-40
Temperature range (fixed) max. [°C]	+80
Temperature range (drag chain) min. [°C]	-30
Temperature range (drag chain) max. [°C]	70
Protection to IEC 60529	IP67
Flame retardant	Yes
PWIS-free	Yes
RoHS compliant	Yes
REACH compliant	Yes
Drag chain-adapted	Yes
Oil resistant	Yes
CE – Market approval for Europe	Yes
UL – Market approval for the United States	Yes
CSA – Market approval for Canada	Yes
EAC – Market approval for Eurasia	Yes
UKCA – Market approval for the United Kingdom	Yes



- ② RD
- ③ BK
- ④ WH
- ⑤ BU

