

Y-PLUG-IN CONNECTOR

CSTE02024

Order no.	CSTE02024
Technical Data	
Fixing thread	M12-M12-M12
Connection type	Socket / pin / pin
Coding	A
Version	Straight/straight/straight
No. of contacts	5 / 5 / 5
Rated voltage [V]	60
Current load (at 40°C) [A]	4
Coupling nut material	Diecast zinc, nickel-plated
Temperature range (fixed) min. [°C]	-25
Temperature range (fixed) max. [°C]	85
Protection to IEC 60529	IP67
PWIS-free	Yes
RoHS compliant	Yes
REACH compliant	Yes

