


# CONNECTING CABLE

## CSTE02025

Order no.	CSTE02025
<b>Technical Data</b>	
Fixing thread	M8-M12
Connection type	Pin / socket
Coding	B / A
Version	Straight/straight
No. of contacts	5 / 5
Rated voltage [V]	30
Current load (at 40°C) [A]	3
Grip body material	PUR
Coupling nut material	Metal, CuZn, nickel-plated
Sealing material	FKM
Cable sheath material	PUR
Cable length [m]	0.15
Cable-Ø [mm]	5.6
Nr. of wires x diameter [mm <sup>2</sup> ]	5x0.25
Bending radius for fixed routing, min.	6xØ
Bending radius when using a drag chain, min.	10xØ
Temperature range (fixed) min. [°C]	-40
Temperature range (fixed) max. [°C]	+90
Temperature range (drag chain) min. [°C]	-30
Temperature range (drag chain) max. [°C]	90
Protection to IEC 60529	IP67
Flame retardant	Yes
PWIS-free	Yes
RoHS compliant	Yes
REACH compliant	Yes
Drag chain-adapted	Yes
Oil resistant	Yes
CE – Market approval for Europe	Yes
UKCA – Market approval for the United Kingdom	Yes



- ① BN
- ② WH
- ③ BU
- ④ BK
- ⑤ GY

