

LOAD RESISTANCE

CSTE02026

Order no.	CSTE02026
Technical Data	
Fixing thread	M12
Connection type	Socket
Coding	A
Version	Straight
No. of contacts	5
Rated voltage [V]	30
Current load (at 40°C) [A]	4
Grip body material	PUR
Coupling nut material	Metal, CuZn, nickel-plated
Temperature range (fixed) min. [°C]	-25
Temperature range (fixed) max. [°C]	85
Protection to IEC 60529	IP67
Weight [kg]	0.022
PWIS-free	Yes
RoHS compliant	Yes
REACH compliant	Yes
CE – Market approval for Europe	Yes
UL – Market approval for the United States	Yes
UKCA – Market approval for the United Kingdom	Yes

