

ENERGY ELEMENT

WER1500FSI08-10-A

Order no.	► Technical Data
Series	WER1500
Transmission mode	electrical
Function	Signal current with direct connection to UR
Compatible with installation size	HWR2031 / HWR2040 / HWR2050 / HWR63-B / HWR80-B / WPR5031-A / WPR5040-A / WPR5050-A / WPR5063-A / WPR5080-A / FWR40-B / FWR50-B / FWR63-B / FWR80-B
Compatible with	Fixed part
No. of contacts	8
Connection type	Spring contacts
Nominal current [A]	1.5
Supply voltage [V]	30
Fixing thread	M8
Connection type	Socket
Connection type	Round plug
Connection alignment	radial </td
Joining force [N]	8
Release force [N]	-
Protection to IEC 60529	IP54*
Weight [kg]	0.042

*only in coupled state

