

# ENERGY ELEMENT

## WER3000LIL01-09-A

Order no.	► Technical Data
Series	WER3000
Transmission mode	electrical
Data transmission	IO-Link
Compatible with installation size	WWR / WWR1000 - 100 / 125 / 160 / 200
Compatible with	Loose part
No. of contacts	5
Connection type	Spring contacts
Nominal current [A]	5
Supply voltage [V]	30
Fixing thread	M12
Coding	A
Connection type	Socket
Connection type	Round plug
Connection alignment	radial or axial
Joining force [N]	10
Release force [N]	-
Protection to IEC 60529	IP54*
Weight [kg]	0.11

\*only in coupled state



