

CHECKLIST

CLAMPING AND BRAKING ELEMENTS

Customer number	<input type="text"/>	Phone number	<input type="text"/>
Company	<input type="text"/>	E-mail	<input type="text"/>
Contact	<input type="text"/>		
	<input type="checkbox"/> Mr	<input type="checkbox"/> Ms	

Processed by	<input type="text"/>	Date	<input type="text"/>
Amount	<input type="text"/>	Desired date	<input type="text"/>
Pot. amount p. a.	<input type="text"/>		

Description of the application

Attached representation

Drawing 3D model

Product type

Clamping element Clamping and braking element

Actuation

Manual Pneumatic Hydraulic Electric

Operating pressure [bar]

Status

Opened without energy (NO) Closed without energy (NC) Bistable (N)

Information on the profile rail guide

Manufacturer Rail type With masking tape

Rail size Carriage type

or

Flat steel Shaft Size/diameter [mm] Tolerance +/- [µm]

Technical data

Installation position Horizontal Vertical At an angle of [°]

Required holding force [N] Cycles per hour/
Service life in cycles

Max. speed of the application [m/s]

Environment

Operating temperature [°C]
 Clean Slightly soiled Soiled

Features

End seal Sensing
 Stainless steel design Alternative power connection
 at the top at the front

Other