

VACUUM GENERATORS

COMPACT EJECTORS - SERIES KE25

▶ PRODUCT SPECIFICATIONS




▶ Special features


- Air consumption optimized by finely adjustable suction capacity
- Electronic vacuum switch (KE25NOE)
- Digital vacuum switch (KE25NOD)
- Significantly reduced compressed air consumption using optional air saving technology

▶ EJECTORS/VACUUM GENERATORS


Pumping speed at different vacuum levels



Evacuation time for different vacuum levels



Reachable vacuum of different operating pressure



▶ RECOMMENDED ACCESSORIES



Straight Fittings - Quick Connect Style

GV1-4X8




Straight Fittings - Barb Style Connection

GV3-8X13ID



Plug-in connector Straight Cable 5m - Socket M8 (female)

KAG500B4



Connecting cable

ZUB0041



Air Saving Function

ZUB0006



Air Connection 4-Connections

ZUB0011

Order no.	Technical Data	
	KE25NOD	KE25NOE
Nozzle diameter [mm]	2.5	2.5
Vacuum level [%]	85	85
Max. suction capacity [l/min]	161	161
Max. suction capacity [m ³ /h]	9.7	9.7
Air consumption suction [l/min]*	310	310
Air consumption suction [m ³ /h]*	18.6	18.6
Air consumption blowing [l/min]	200	200
Noise level (suction) [db(A)]	72	72
Noise level (free-running) [db(A)]	82	82
Operating pressure [bar]	5 ... 6	5 ... 6
Recommended inner hose Ø compressed air [mm]**	6	6
Recommended inner hose Ø vacuum [mm]**	9	9
Operating temperature [°C]	0 ... +45	0 ... +45
Weight [kg]	0.485	0.485

*at 5 bar operating pressure

**at max. 2m Length

